

PRESTO W92 Process system

The W92 class process systems are extremely powerful and can also simulate extreme environmental conditions. They are used, for example, in the temperature control of vacuum chambers for component testing in the aerospace industry.


The highly dynamic temperature control systems PRESTO are designed for high-precision temperature control for a wide range of applications such as reactor vessels or material stress tests. Moreover, by using efficient components, the process systems can compensate exothermic and endothermic reactions exceptionally fast. Permanent internal monitoring and self-lubricating pumps ensure a long life-time. In addition, numerous interfaces offer many remote control possibilities across networks or for integration into higher-level control systems.



Product features


- Cooling capacity up to 31 kW
- Ambient temperature range +5 °C to +40 °C
- Optional analog connections, RS485, Profibus DP, Modbus
- External Pt100 sensor connection
- Analog connections, RS485, Profibus DP (accessory)
- Built-in 5.7" industrial color touchscreen
- Alarm output
- Second external Pt100 sensor connection (accessory)
- Intelligent warning and safety functions
- Pump pressure up to 3 bar, max. flow rate 80 l/min

Cool-down time




Medium: Thermal HL

Heat-up time



Medium: Thermal HL

Pump capacity



Performance values

400V/3PNPE/50Hz (Without Plug)	
Heating capacity kW	18
Viscosity max. cSt	50
Pump capacity flow rate l/min	0 ... 80
Pump capacity flow pressure bar	0.1 ... 3
Power consumption A	43

Refrigerant variants

Order No.		9421922.07				
Cooling capacity (Ethanol)						
°C	20	0	-20	-40	-60	-80
kW ¹	27	20	11	10.5	8	2
Refrigerant stage 1			Refrigerant stage 2			
Refrigerant	R404A		Refrigerant	R23		
Filling weight g	4500		Filling weight g	1250		
Global Warming Potential for R404A	3922		Global Warming Potential for R23	14800		
Carbon dioxide equivalent t	17.649		Carbon dioxide equivalent t	18.5		

Order No.		9421922.S1.07					
Cooling capacity (Ethanol)							
°C	20	0	-20	-40	-60	-80	-90
kW ¹	26	17	11	10.5	8	2	0.8
Refrigerant stage 1				Refrigerant stage 2			
Refrigerant	R449A			Refrigerant	R23		
Filling weight g	4500			Filling weight g	1250		
Global Warming Potential for R449A	1397			Global Warming Potential for R23	14800		
Carbon dioxide equivalent t	6.2865			Carbon dioxide equivalent t	18.5		

¹ Performance specifications measured in accordance with DIN 12876. Cooling capacities up to 20 °C measured with ethanol; over 20 °C with thermal oil unless otherwise specified. Performance specifications apply at an ambient temperature of 20 °C. Performance values may differ with other bath fluids.

Technical data

Available voltage versions		Cooling	
Order No.	9 421 922	Cooling of compressor	2-stage Water
Available voltage versions:		Cooling water pressure max. bar	6
9421922.07	400V/3PNPE/50Hz (Without Plug) (R404A)	Max. heat dissipated by unit into cooling water kW	50
9421922.S1.07	400V/3PNPE/50Hz (Without Plug) (R449A)	Recommended cooling water properties	
9421922.17	480V/3P(N)PE/60Hz (Without Plug) (R404A)	Cooling water temperature range °C	10 ... 15
		Cooling water difference pressure bar	1.5 ... 6
		Cooling water consumption l/min ²	43
		Permissible cooling water properties	

Cooling water temperature range °C	5 ... 35
Cooling water difference pressure bar ³	0.5 ... 6

² Cooling water consumption may vary outside recommended cooling water properties.

³ At cooling water temperatures of 25 °C and higher, the minimum differential pressure is 1 bar.

Other	
Sound pressure level dbA	74
Classification	Classification III (FL)
IP Code	IP 21
Pump type	Centrifugal Pump
Pump type Magnetically coupled	1

Electronics	
Interfaces	Alarm output, Ethernet, Modbus, RS232, SD memory card, USB
External pt100 sensor connection	integrated
2nd external Pt100 sensor connection	accessory
Integrated programmer	8x60 steps
Temperature control	ICC
Absolute temperature calibration	3 Point Calibration
Temperature display	5.7" TFT Touchscreen
Temperature setting	Touchscreen

Dimensions and volumes	
Internal usable expansion volume l	40
Minimal process volume l	28
Active heat exchanger volume l	16
Weight kg	870
Cooling Water Connection in	G ^{3/4}
Dimensions cm (W x L x H)	95 x 127 x 190
Pump connections	M38x1.5 male

Temperature values	
Setting the resolution of the temperature display °C	0.01
Working temperature range °C	-92 ... +250
Temperature stability °C	±0.05 ... ±0.2
Ambient temperature °C	+5 ... +40
Setting the resolution of the temperature display °C	0.01

All Benefits



Green technology.
Development consistently applied environmentally friendly materials and technologies.



Touch display. Perfect operation.
With the touch display, the user always has an overview of all values and functions. The intuitive and multilingual menu structure enables perfect control.



Convenience for several users
Administrator level for customizing instrument settings, user levels with limited permissions for fast and safe defined access, password protection, all levels adjustable



100 % Cooling capacity
'Active Cooling Control' for cooling available throughout the entire working temperature range, fast cool-down even at higher temperatures



Intelligent temperature control.
Intelligent cascade control - automatic and self-optimizing adaptation of the PID control parameters with external stability of +/- 0.05 °C.



Full control
'Temperature Control Features', for individual optimization, access to all important control parameters, additional settings for band limit, limits, co-speedfactor etc.



Control of the external application
External Pt100 sensor connection for precise measurement and control directly in the external application



Highest measuring accuracy
'Absolute Temperature Calibration' for manual compensation of a temperature difference, 3-point calibration



Intelligent pump system
Reliable and consistent pump capacity, electronically adjustable pump stages or pressure value, automatic adjustment of pump capacity to viscosity



Many interfaces.
Straight-forward remote control, data management, and integration into process structures. USB, Ethernet, RS232, SD card, and alarm off are permanently integrated. Further interfaces available as accessories.



Space-saving footprint
All connections as well supply and exhaust air are located at the front or rear, no venting grids on the sides, units can be placed close to each other or the application



Continuous operation up to +40 °C
Robust temperature control instrument, continuous operation even at ambient temperatures of up to +40 °C



Maximum safety.
Classification III according to DIN12876-1 enables safe operation, even with flammable fluids. Automatic switch-off in the event of high temperature or low liquid level.



Duplicate safety
Adjustable high temperature cut-off for internal tank and for integrated expansion vessel



For flammable bath fluid
Classification III (FL) according to DIN 12876-1



100% Checked.
100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.



Quick support
If an error occurs, the integrated Black-Box function permits fast diagnosis by the JULABO service team



JULABO. Quality.
Highest standards of quality for a long product life.



Quick start.
Individual JULABO consultation and comprehensive manuals at your disposal.



Satisfied customers.
11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



Services 24/7.
Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at www.julabo.com.