

Model BD 260 | Standard-Incubators with natural convection

The BD Avantgarde. Line series is specially designed for gentle incubation of organisms, as well as conditioning of heat-sensitive media. The new design of the units and the homogeneous temperature distribution ensure the very best results.

BENEFITS

- · Excellent temporal and spatial temperature accuracy
- High process reliability
- 100°C disinfection routine



Model 260



Model 260

IMPORTANT FEATURES

- Temperature range: +5°C above ambient temperature to +100°C
- High temperature accuracy thanks to APT.line™ technology
- Natural convection
- Controller with LCD display
- Electromechanical control of the exhaust air flap
- Inner door made of tempered safety glass

- 2 chrome-plated racks
- Class 3.1 integrated independent temperature safety device (DIN 12880) with visual alarm
- Ergonomic handle design
- USB port for recording data

ORDERING INFORMATION

Interior volume [L]	Power supply - unit fuse	Plug*	Version	Model version	ArtNo.
Model BD 260					
	230 V 1~ 50/60 Hz -8,0 A	CEE 7/7	Standard	BD260-230V	9010-0329
253	120 V 1~ 60 Hz -12,5 A	NEMA 5-15	Standard	BD26oUL-12oV	9010-0330



TECHNICAL DATA


TECHNICAL DATA		
Data		
Designation	BD260-230V	BD26oUL-12oV
Article Number	9010-0329	9010-0330
Option model	Standard	Standard
Performance Data Temperature		
Temperature range	+5 °C above ambient temperature to 100 °C	+5 °C above ambient temperature to 100 °C
Temperature uniformity at 37°C	0.3 ± K	0.3 ± K
Temperature uniformity at 100°C	1.0 ± K	1.0 ± K
Temperature fluctuation at 37°C	0.2 ± K	0.2 ± K
Temperature fluctuation at 100°C	0.5 ± K	0.5 ± K
Heating up time to 100°C	75 min	75 min
Heating up time to 37°C	6o min	6o min
Recovery time after door was opened for 30 s at 37°C	16 min	16 min
Electrical data		
Rated Voltage	230 V	120 V
Power frequency	50/60 Hz	60 Hz
Nominal power	o,85 kW	0,95 kW
Unit fuse	8,0 A	12,5 A
Phase (Nominal voltage)	1~	1~
Dimensions and weights		
Interior volume	253 L	253 L
Net weight of the unit (empty)	85 kg	85 kg
Load per rack	40 kg	40 kg
Permitted load	270 kg	270 kg
Wall clearance back	160 mm	160 mm
Wall clearance sidewise	100 mm	100 mm
Housing dimensions not incl. fittings and connections		
Width net	810 mm	810 mm
Height net	940 mm	940 mm



Depth net	760 mm	760 mm
Internal Dimensions		
Interior width	610 mm	610 mm
Interior height	760 mm	760 mm
Interior depth	545 mm	545 mm
Inner doors	1	1
Unit doors	1	1
Environment-specific data		
Energy consumption at 100°C	225 Wh/h	225 Wh/h
Energy consumption at 37°C	40 Wh/h	40 Wh/h
Fixtures		
Number of shelves (std./max.)	2/8	2/8

All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10%. The temperature data is determined to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

DIMENSIONS Incl. fittings and connections [mm]



OPTIONS

Designation	Description	BD 260	*	ArtNo.
Access port with silicone plug	back			
	10 mm	•	01	8012-0390
	30 mm	•	01	8012-0397
	50 mm	•	01	8012-0399
	left			
	10 mm	•	01	8012-0388
	30 mm	•	01	8012-0047
	50 mm	•	01	8012-0051



Designation	Description	BD 260	*	ArtNo.
	right			
	10 mm	•	01	8012-0387
	30 mm	•	01	8012-0046
	50 mm	•	01	8012-0050
	top			
	10 mm	•	01	8012-0386
	30 mm	•	01	8012-0045
	50 mm	•	01	8012-0049
	100 mm	•	01	8012-0053
Alarm function for overheating	Switchable acoustic alarm, with adjustable limit value on the independent temperature safety device	•	-	8012-0979
Analog output 4-20 mA	for temperature values (output not adjustable)	•	02	8012-0941
Calibration certificate, expanded	for temperature; for extending the measurement in center of chamber to include another test temperature	•	-	8012-1110
	for temperature, measurement in center of chamber at specified temperature	•	-	8012-1129
Calibration certificate,	temperature measurement incl. certificate, 9 measuring points at specified temperature	•	-	8012-0915
temperature	temperature measurement incl. certificate, 15-18 measuring points at specified temperature	•	-	8012-0918
	temperature measurement incl. certificate and 27 measuring points at specified temperature	•	-	8012-0921
Clock	battery-backed	•	-	8012-0981
Door lock	lockable door handle	•	-	8012-1025
Ethernet interface	for Multi Management Software APT-COM™	•	-	8012-0986
Pt 100 temperature sensor	additional flexible Pt 100, interior, for displaying the temperature on the unit display	•	-	8012-0940

ACCESSORIES

Designation	Description	BD 260	*	ArtNo.
	for simple logging and documentation requirements with up to 5 networked units.			
APT-COM™ 4 BASIC-Edition	version 4, BASIC edition	•	-	9053-0039
APT-COM™ 4 GLP-Edition	for working under GLP-compliant conditions. Measured values are documented in a tamper- proof way in line with the requirements of FDA Regulation 21 CFR 11.			
	version 4, GLP edition	•	-	9053-0042



Description	BD 260	*	ArtNo.
convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.			
version 4, PROFESSIONAL edition	•	-	9053-0040
concentrated, for gentle remove of residual contaminants; 1 kg	•	-	8012-2250
IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO_2 , O_2 – or pressure, depending on unit			
Digital in PDF format	•	-	7057-0005
Hard copy inside folder	•	-	7007-0005
IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO ₂ , O ₂ , pressure, depending on unit			
Digital in PDF format	•	-	7057-0001
Hard copy inside folder	•	-	7007-0001
max. load per rack 40 kg			
chrome plated	•	-	8012-2043
stainless steel	•	-	8012-2173
max. load per rack 70 kg			
Stainless steel	•	-	8012-2187
Rubber pads set anti-slip feet		-	8012-2030
max. load per rack 40 kg			
Stainless steel	•	-	8012-2181
stable cart, casters with locking brakes, dimensions: W 1,300 x D 800 x H 780 mm	•	-	9051-0019
	version 4, PROFESSIONAL edition concentrated, for gentle remove of residual contaminants; 1 kg IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO ₂ , O ₂ – or pressure, depending on unit Digital in PDF format Hard copy inside folder IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO ₂ , O ₂ , pressure, depending on unit Digital in PDF format Hard copy inside folder max. load per rack 40 kg chrome plated stainless steel max. load per rack 70 kg Stainless steel set anti-slip feet max. load per rack 40 kg - Stainless steel	to 100 units. version 4, PROFESSIONAL edition concentrated, for gentle remove of residual contaminants; 1 kg . Q/OQ/PQ documents — supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ: parameters: temperature, CO ₂ , O ₂ — or pressure, depending on unit Digital in PDF format Hard copy inside folder . Q/OQ documents — supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation: parameters: temperature, CO ₂ , O ₂ , pressure, depending on unit Digital in PDF format Hard copy inside folder max. load per rack 40 kg chrome plated stainless steel max. load per rack 70 kg Stainless steel set anti-slip feet max. load per rack 40 kg Stainless steel set anti-slip feet max. load per rack 40 kg Stainless steel .	to 1000 units. version 4, PROFESSIONAL edition concentrated, for gentle remove of residual contaminants; 1 kg . CONCENTRATE SUPPORTING documents or validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO ₂ , O ₂ – or pressure, depending on unit Digital in PDF format Hard copy inside folder IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO ₂ , O ₂ , pressure, depending on unit Digital in PDF format Hard copy inside folder max. load per rack 40 kg chrome plated stainless steel max. load per rack 70 kg Stainless steel set anti-slip feet max. load per rack 40 kg Stainless steel set anti-slip feet max. load per rack 40 kg Stainless steel set anti-slip feet max. load per rack 40 kg Stainless steel set anti-slip feet max. load per rack 40 kg

SERVICES

Designation	Description	*	ArtNo.
Calibration services			
	Calibration of one (1) test temperature specified by the user in center of chamber, including certificate	-	DL30-0110
Calibration certificate, temperature	Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate	-	DL30-0102
Temperature measurement, 9 measuring points	Temperature measurement with 9 measuring points with a set value specified by the user, including certificate	_	DL30-0109
Temperature measurement, 18 measuring points	Temperature measurement with 18 measuring points with a set value specified by the user, including certificate	-	DL30-0118



Designation	Description	*	Art No.
Designation	Description		ArtNo.
Temperature measurement, 27 measuring points	Temperature measurement with 27 measuring points with a set value specified by the user, including certificate	-	DL30-0127
Installation services			
Unit commissioning	Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	-	DL10-0100
Unit instructions	Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	-	DL10-0500
Maintenance contracts			
BRONZE 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts	-	DL20-0720
GOLD 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate	-	DL20-0915
SILVER 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate	-	DL20-0815
Maintenance services			
Maintenance	One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate	-	DL20-0601
Validation services			
Execution of IQ/OQ	Execution of IQ/OQ in accordance with qualification folder	-	DL40-0100
Execution of IQ/OQ/PQ	Execution of IQ/OQ/PQ in accordance with qualification folder	-	DL44-0500
Warranty service			
1-year warranty extension	The warranty is extended by 1 year from the delivery date, wear parts are excluded	-	DL50-0010



NOTES

- O1 Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.
- 02 UL mark is not granted when this option is used.

BINDER GmbH

Tuttlingen, Germany TEL +49 7462 2005 0 info@binder-world.com www.binder-world.com BINDER Inc.

Bohemia, NY, USA TEL +1 631 224 4340 usa@binder-world.com www.binder-world.us BINDER Environmental Testing Equipment (Shanghai) Co., Ltd.

Shanghai, P.R. China TEL +86 21 685 808 25 china@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China TEL +852 39070500 asia@binder-world.com www.binder-world.com