## Hei-VAP Core - hand lift model with G3 XL vertical glassware



An operating concept that is focused on the essentials: clear and with access to the basic parameters rotation speed and heating bath temperature at any time.

- Clear digital display showing actual and set values
- Two separate knobs with dynamic control for setting the rotation speed and heating bath temperature: fast turning for large jumps, slow turning for precise setting of the set values
- Accidental changing of the values can be prevented by the lock function
- Intuitive LED ring light system makes activated functions clearly visible even from a distance
- Easy adjustment of the immersion depth up to 160 mm and the inclination angle from 20° to 80°
- Standby function and residual heat warning at heating bath temperatures above 50 °C
- Hand lift model with G3 XL vertical glassware achieve higher evaporation rates due to expanded cooling surface of 2,200 cm<sup>2</sup>
- The standby button stops all functions.



## Hei-VAP Core - Technical Data

| Rotation speed indicator                           | 3.5" LCD Display                                                                                |
|----------------------------------------------------|-------------------------------------------------------------------------------------------------|
| Permissible ambient conditions                     | 5 – 31 °C at 80 % rel. humidity<br>32 – 40 °C decreasing lineary up to max 50%<br>rel. humidity |
| Protection class DIN EN 60529                      | IP 20                                                                                           |
| Lift                                               | Hand lift                                                                                       |
| Height adjustment speed                            | manual                                                                                          |
| Height adjustment                                  | 155 mm                                                                                          |
| Drive                                              | brushless DC motor with electronic speed control                                                |
| Heating capacity                                   | 1,300 W                                                                                         |
| Temp. range heating bath                           | 20 - 210 °C                                                                                     |
| Temperature accuracy bath                          | ±1K                                                                                             |
| Overheat protection bath                           | cut-off at 5 °C over set temperature via separate PT 1000                                       |
| Bath temperature setting                           | 3.5" LCD Display                                                                                |
| Heating bath temperature control                   | electronic / digital                                                                            |
| Secondary overtemp. cut off                        | 250 °C                                                                                          |
| Material heating bath                              | stainless steel AISI 316L                                                                       |
| Diameter heating bath                              | 255 mm                                                                                          |
| Volume heating bath                                | 4.5                                                                                             |
| Display vapor temperature                          | -                                                                                               |
| Required accessories for display vapor temperature | _                                                                                               |
| Integrated vacuum controller                       | -                                                                                               |
| Timer                                              | -                                                                                               |
| Programmable ramps                                 | -                                                                                               |
| Supply Power                                       | 1,400 W                                                                                         |
| Weight without glassware assembly                  | 16 kg                                                                                           |



## Premium Laboratory Equipment

| Dimensions with glassware set G3 (w/d/h)             | max. 739 x 477 x 845 mm |
|------------------------------------------------------|-------------------------|
| Dimensions with glassware set G3 XL (w/d/h)          | max. 739 x 477 x 920 mm |
| Condensing surface                                   | 1,400 cm <sup>2</sup>   |
| Condensing surface XL condenser                      | 2,200 cm <sup>2</sup>   |
| Max. size evaporating flask                          | 51                      |
| Rotation speed range                                 | 10 - 280 rpm            |
| Integrated Hei-CHILL controller                      | -                       |
| Vacuum program DAA mode requires AUTOaccurate-Sensor | _                       |
| Solvent libary                                       | -                       |

