

Hei-VAP Core - hand lift model with coated G5 dry ice condenser



An operating concept that is focused on the essentials: clear and with access to the basic parameters rotation speed and heating bath temperature at any time.

- Clear digital display showing actual and set values
- Two separate knobs with dynamic control for setting the rotation speed and heating bath temperature: fast turning for large jumps, slow turning for precise setting of the set values
- Accidental changing of the values can be prevented by the lock function
- Intuitive LED ring light system makes activated functions clearly visible even from a distance
- Easy adjustment of the immersion depth up to 160 mm and the inclination angle from 20° to 80°
- Standby function and residual heat warning at heating bath temperatures above 50 °C
- Hand lift model with transparent plastic coated G5 dry ice condenser
- The standby button stops all functions.

Hei-VAP Core - Technical Data

| | |
|--|--|
| Rotation speed indicator | 3.5" LCD Display |
| Permissible ambient conditions | 5 – 31 °C at 80 % rel. humidity 32 – 40 °C decreasing lineary up to max 50% rel. humidity |
| Protection class DIN EN 60529 | IP 20 |
| Lift | Hand lift |
| Height adjustment speed | manual |
| Height adjustment | 155 mm |
| Drive | brushless DC motor with electronic speed control |
| Heating capacity | 1,300 W |
| Temp. range heating bath | 20 – 210 °C |
| Temperature accuracy bath | ±1K |
| Overheat protection bath | cut-off at 5 °C over set temperature via separate PT 1000 |
| Bath temperature setting | 3.5" LCD Display |
| Heating bath temperature control | electronic / digital |
| Secondary overtemp. cut off | 250 °C |
| Material heating bath | stainless steel AISI 316L |
| Diameter heating bath | 255 mm |
| Volume heating bath | 4.5 l |
| Display vapor temperature | - |
| Required accessories for display vapor temperature | - |
| Integrated vacuum controller | - |
| Timer | - |
| Programmable ramps | - |
| Supply Power | 1,400 W |
| Weight without glassware assembly | 16 kg |

| | |
|---|-------------------------|
| Dimensions with glassware set G3 (w/d/h) | max. 739 x 477 x 845 mm |
| Dimensions with glassware set G3 XL (w/d/h) | max. 739 x 477 x 920 mm |
| Condensing surface | 1,400 cm ² |
| Condensing surface XL condenser | 2,200 cm ² |
| Max. size evaporating flask | 5 l |
| Rotation speed range | 10 - 280 rpm |
| Integrated Hei-CHILL controller | - |
| Vacuum program DAA mode requires AUTOaccurate-Sensor | - |
| Solvent library | - |