Hei-VAP Ultimate - hand lift model with G3 vertical glassware $_{\text{P/N:}\ 575\text{-}01300\text{-}00}$



Precise setting of rotation speed and heating bath temperature on the digital touch display or – for quick access during an active process – directly via the knobs on the operating panel.

- Central operating panel with 7" touch display
- Hand lift model with G3 vertical glassware
- Clear display of all values (Basic and Advanced modes)
- With timer, limitation of max. temperature, multilingual menu and text display for error messages
- Separate knobs for rotation and heating with locking function to prevent accidental readjusting
- LED ring lights and pictogram to display the activity even from a distance
- Integrated solvent library to facilitate adjustment of the required vacuum on an external vacuum controller
- USB and Micro SD plus LAN / RS 232 interfaces (Lab 4.0 ready)
- Optional display of vapor temperature
- Subsequent upgrade to Hei-VAP Ultimate Control possible, including vacuum and chiller control

Hei-VAP Ultimate - Technical Data

Rotation speed indicator	7" LCD color graphic display
Permissible ambient conditions	5 – 31 °C at 80 % rel. humidity 32 – 40 °C decreasing lineary up to max 50% rel. humidity
Protection class DIN EN 60529	IP 20
Lift	Hand lift
Height adjustment speed	manual
Height adjustment	155 mm
Drive	brushless DC motor with electronic speed control
Heating capacity	1,300 W
Temp. range heating bath	20 – 210 °C
Temperature accuracy bath	±1K
Overheat protection bath	cut-off at 5 °C over set temperature via separate PT 1000
Bath temperature setting	7" LCD color graphic display
Heating bath temperature control	electronic / digital
Secondary overtemp. cut off	250 °C
Material heating bath	stainless steel AISI 316L
Diameter heating bath	255 mm
Volume heating bath	4.5
Display vapor temperature	Yes
Required accessories for display vapor temperature	Vapor temperature sensor
Integrated vacuum controller	-
Timer	Yes
Programmable ramps	Yes
Supply Power	1,400 W
Weight without glassware assembly	15 kg

Dimensions with glassware set G3 (w/d/h)	739 x 532 x 887 mm
Dimensions with glassware set G3 XL (w/d/h)	739 x 532 x 920 mm
Condensing surface	1,400 cm ²
Condensing surface XL condenser	2,200 cm ²
Max. size evaporating flask	5
Rotation speed range	10 - 280 rpm
Integrated Hei-CHILL controller	-
Vacuum program Dynamic AUTOaccurate requires AUTOaccurate sensor	_
Solvent libary	Yes