

## Hei-VAP Expert Control - hand lift model with coated G3 XL vertical glassware

P/N: 573-02315-00



Adds numerous smart features to the Hei-VAP Expert, as well as an overview of all parameters and the current process

- 5" touch display for controlling the entire system including the vacuum and the cooling temperature
- Hand lift model with transparent plastic coated G3 XL vertical glassware - achieve higher evaporation rates due to expanded cooling surface of 2,200 cm<sup>2</sup>
- For precise monitoring, the pictogram on the display also symbolizes active functions
- Separate knobs for quick access: the right one for direct vacuum control, the left one for the rotation
- Setting of values either via the touch display or the separate quick access knobs
- Direct access to two favorites on the start screen
- Expandable solvent library. You can also transfer your own favorites to other devices using a USB stick
- Define and save own evaporation processes (ramps)
- Automatically evaporate with the Dynamic AUTOaccurate Program (DAA). Convenient and customizable: from foam avoidance to highly efficient evaporation

- With USB and Micro SD interface for easy installation of software updates and transfer of individual favorites from one device to another

## Hei-VAP Expert Control - Technical Data

|  |  |
|--|--|
| Rotation speed indicator                           | 5" LCD color graphic display   |
| Permissible ambient conditions                     | 5 – 31 °C at 80 % rel. humidity<br>32 – 40 °C decreasing lineary up to max 50% rel. humidity |
| Protection class DIN EN 60529                      | IP 20  |
| Lift   | Hand lift  |
| Height adjustment speed                            | manual   |
| Height adjustment                                  | 155 mm   |
| Drive  | brushless DC motor with electronic speed control   |
| Heating capacity                                   | 1,300 W  |
| Temp. range heating bath                           | 20 – 210 °C  |
| Temperature accuracy bath                          | ±1K  |
| Overheat protection bath                           | cut-off at 5 °C over set temperature via separate PT 1000                                    |
| Bath temperature setting                           | 5" LCD color graphic display   |
| Heating bath temperature control                   | electronic / digital   |
| Secondary overtemp. cut off                        | 250 °C   |
| Material heating bath                              | stainless steel AISI 316L  |
| Diameter heating bath                              | 255 mm   |
| Volume heating bath                                | 4.5 l  |
| Display vapor temperature                          | Yes  |
| Required accessories for display vapor temperature | Vapor temperature sensor   |
| Integrated vacuum controller                       | Yes  |
| Timer  | Yes  |
| Programmable ramps                                 | Yes  |
| Supply Power                                       | 1,400 W  |
| Weight without glassware assembly                  | 15 kg  |

|   |                       |
|---|-----------------------|
| Dimensions with glassware set G3 (w/d/h)                            | 739 x 532 x 887 mm    |
| Dimensions with glassware set G3 XL (w/d/h)                         | 739 x 532 x 920 mm    |
| Condensing surface  | 1,400 cm <sup>2</sup> |
| Condensing surface XL condenser                                     | 2,200 cm <sup>2</sup> |
| Max. size evaporating flask   | 5 l                   |
| Rotation speed range  | 10 - 280 rpm          |
| Integrated Hei-CHILL controller                                     | Yes                   |
| Vacuum program Dynamic AUTOaccurate<br>requires AUTOaccurate sensor | Yes                   |
| Solvent library   | Yes                   |