## Hei-VAP Expert Control - motor lift model with G5 dry ice condenser P/N: 574-02500-00



Adds numerous smart features to the Hei-VAP Expert, as well as an overview of all parameters and the current process

- 5" touch display for controlling the entire system including the vacuum and the cooling temperature
- Motor lift model with G5 dry ice condenser
- For precise monitoring, the pictogram on the display also symbolizes active functions
- Separate knobs for quick access: the right one for direct vacuum control, the left one for the rotation
- Setting of values either via the touch display or the separate quick access knobs
- Direct access to two favorites on the start screen
- Expandable solvent library. You can also transfer your own favorites to other devices using a USB stick
- Define and save own evaporation processes (ramps)
- Automatically evaporate with the Dynamic AUTOaccurate Program (DAA). Convenient and customizable: from foam avoidance to highly efficient evaporation
- With USB and Micro SD interface for easy installation of software updates and transfer of individual favorites from one device to another

Premium Laboratory Equipment

## Hei-VAP Expert Control - Technical Data

	31 °C at 80 % rel. humidity
	- 40 °C decreasing lineary up to max 50% numidity
Protection class DIN EN 60529 IP 20	0
ift Moto	or lift
Height adjustment speed 25 m	nm/s
Height adjustment 155	mm
Drive brus cont	chless DC motor with electronic speed crol
Heating capacity 1,30	0 W
emp. range heating bath 20 -	· 210 °C
emperature accuracy bath ±1K	
	off at 5 °C over set temperature via arate PT 1000
Bath temperature setting 5" LC	CD color graphic display
Heating bath temperature control elect	tronic / digital
Secondary overtemp. cut off 250	°C
Material heating bath stair	nless steel AISI 316L
Diameter heating bath 255	mm
/olume heating bath 4.5 I	
Display vapor temperature Yes	
Required accessories for display vapor Vapo emperature	or temperature sensor
ntegrated vacuum controller Yes	
imer Yes	
Programmable ramps Yes	
Supply Power 1,40	0 W
Veight without glassware assembly 15 kg	g

## Premium Laboratory Equipment

Dimensions with glassware set G3 (w/d/h)	739 x 477 x 887 mm
Dimensions with glassware set G3 XL (w/d/h)	739 x 477 x 920 mm
Condensing surface	1,400 cm <sup>2</sup>
Condensing surface XL condenser	2,200 cm²
Max. size evaporating flask	51
Rotation speed range	10 - 280 rpm
Integrated Hei-CHILL controller	Yes
Vacuum program Dynamic AUTOaccurate requires AUTOaccurate sensor	Yes
Solvent libary	Yes