Hei-VAP Ultimate Control - hand lift model with G1 diagonal glassware $_{\text{P/N:}\ 575\text{-}02100\text{-}00}$



Adds numerous smart features to the Hei-VAP Ultimate, as well as an overview of all parameters and the current process

- 7" touch display for controlling the entire system including the vacuum and the cooling temperature
- Hand lift model with G1 diagonal glassware
- For precise monitoring, the pictogram on the display also symbolizes active functions
- Separate knobs for quick access: the right one for direct vacuum control, the left one for the rotation
- Setting of values either via the touch display or the separate quick access knobs
- Direct access to two favorites on the start screen
- Expandable solvent library. You can also transfer your own favorites to other devices using a USB stick
- Define and save own evaporation processes (ramps)
- Automatically evaporate with the Dynamic AUTOaccurate Program (DAA). Convenient and customizable: from foam avoidance to highly efficient evaporation
- USB and Micro SD plus LAN / RS 232 interfaces (Lab 4.0 ready)

Hei-VAP Ultimate Control - Technical Data

Protection class DIN EN 60529 IP	– 31 °C at 80 % rel. humidity 2 – 40 °C decreasing lineary up to max 50% el. humidity 20
	· 20
Lift Ha	and lift
Height adjustment speed ma	nanual
Height adjustment 15	55 mm
	rushless DC motor with electronic speed ontrol
Heating capacity 1,3	300 W
Temp. range heating bath20	0 – 210 °C
Temperature accuracy bath ±1	1K
	ut-off at 5 °C over set temperature via eparate PT 1000
Bath temperature setting 7"	' LCD color graphic display
Heating bath temperature control ele	ectronic / digital
Secondary overtemp. cut off 25	50 °C
Material heating bath sta	ainless steel AISI 316L
Diameter heating bath 25	55 mm
Volume heating bath 4.5	51
Display vapor temperature Ye	es
Required accessories for display vapor Va temperature	apor temperature sensor
Integrated vacuum controller Ye	es
Timer Ye	es
Programmable ramps Ye	es
Supply Power 1,4	400 W
Weight without glassware assembly 15	5 kg

Dimensions with glassware set G3 (w/d/h)	739 x 532 x 887 mm
Dimensions with glassware set G3 XL (w/d/h)	739 x 532 x 920 mm
Condensing surface	1,400 cm ²
Condensing surface XL condenser	2,200 cm ²
Max. size evaporating flask	5
Rotation speed range	10 - 280 rpm
Integrated Hei-CHILL controller	Yes
Vacuum program Dynamic AUTOaccurate requires AUTOaccurate sensor	Yes
Solvent libary	Yes