# Julabo

# PRESTO W93x Process system

W93 process systems offer users high cooling capacity for dynamic applications even in the lowest temperature ranges. They work with natural refrigerants and are also very energy efficient thanks to state-of-the-art technologies.


The highly dynamic temperature control systems PRESTO are designed for high-precision temperature control for a wide range of applications such as reactor vessels or material stress tests. Moreover, by using efficient components, the process systems can compensate exothermic and endothermic reactions exceptionally fast. Permanent internal monitoring and self-lubricating pumps ensure a long life-time. In addition, numerous interfaces offer many remote control possibilities across networks or for integration into higher-level control systems.



### Product features

- External Pt100 sensor connection
- Alarm output
- Second external Pt100 sensor connection (accessory)
- Built-in 5.7" industrial color touchscreen
- Cooling capacity up to 19.5 kW
- Heating capacity up to 27 kW
- Analog connections, RS485, Profibus DP (accessory)
- Temperature stability ±0.05 °C ... ±0.2 °C
- Integrated gas warning sensor, electrically wired and calibrated
- Intelligent warning and safety functions
- Ambient temperature range +5 °C to +40 °C
- Pump pressure up to 5.5 bar, max. flow rate 70 l/min

#### Pump capacity





#### Performance values

400V/3PNPE/50Hz (Without Plug)			
Heating capacity kW	27		
Viscosity max. cSt	70		
Pump capacity flow rate I/min	0 70		
Pump capacity flow pressure bar	0.1 5.5		
Power consumption A	87		

Order No.	9421933.N1.07					
Cooling capacity (Ethanol)						
°C	20	0	-20	-40	-60	-80
kW <sup>1</sup>	19.5	19.5	19.5	19.5	13	3.5

Note about natural refrigerants:

Temperature control units using natural refrigerants are often subject to regulatory requirements regarding the installation site, operation, transport or disposal of the units. If you have any questions, we will be happy to advise you.

Refrigerant stage 1		Refrigerant stage 2	
Refrigerant	R1270	Refrigerant	R170
Filling weight g	999	Filling weight g	999
Global Warming Potential for R1270	2	Global Warming Potential for R170	6
Carbon dioxide equivalent t	0.001998	Carbon dioxide equivalent t	0.005994

<sup>1</sup> Performance specifications measured in accordance with DIN 12876. Cooling capacities up to 20 °C measured with ethanol; over 20 °C with thermal oil unless otherwise specified. Performance specifications apply at an ambient temperature of 20 °C. Performance values may differ with other bath fluids.

#### **Technical data**

Available voltage versions		Cooling		
Order No.	9 421 933	Cooling of compressor	2-stage Water	
Available voltage versions:		Cooling water pressure max. bar	6	
9421933.N1.07	400V/3PNPE/50Hz (Without Plug) (R1270)	Max. heat dissipated by unit into cooling water kW	53	
9421933.N1.17	480V/3P(N)PE/60Hz (Without Plug)	Recommended cooling water properties		
	(R1270)	Cooling water temperature range °C	10 15	
		Cooling water difference pressure bar	1.5 6	
		Cooling water consumption l/min <sup>2</sup>	40	
		Permissible cooling water properties		
		Cooling water temperature range °C	5 30	
		Cooling water difference pressure bar <sup>3</sup>	0.5 6	
		<ul> <li><sup>2</sup> Cooling water consumption may vary outside recommended cooling water properties.</li> <li><sup>3</sup> At cooling water temperatures of 25 °C and higher, the minimum differential pressure is 1 bar.</li> </ul>		
Other		Electronics		

Sound pressure level dbA	78		
Classification	Classification III (FL)		
IP Code	IP 20		



Pump type Magnetically coupled	Gear Pump 1	Interfaces	Alarm output, Ethernet, Modbus, Profibus optional, REG/EPROG optional, RS232, RS485 optional, SD memory card, Standby- Input optional, USB	
		External pt100 sensor connection	integrated	
		2nd external Pt100 sensor connection	accessory	
		Integrated programmer	8x60 steps	
		Temperature control	ICC	
		Absolute temperature calibration	3 Point Calibration	
		Temperature display	5.7" TFT Touchscreen	
		Temperature setting	Touchscreen	
Dimensions and volumes		Temperature values		
Internal usable expansion volume I	36	Setting the resolution of the temperature	0.01	
Minimal process volume I	30	display °C		
Active heat exchanger volume I	11	Working temperature range °C	-93 +250	
Weight kg	950	Temperature stability °C	±0.05 ±0.2	
Cooling Water Connection in	G¾	Ambient temperature °C	+5 +40	
Dimensions cm (W × L × H)	93 x 138 x 192	Setting the resolution of the temperature display °C	0.01	
Pump connections	M38x1.5 male			

## All Benefits



#### Integrated gas detection sensor

For a high personal and process safety, the new W93 series is equipped with a gas detection sensor. The sensor is already electrically wired and calibrated upon delivery.



#### Services 24/7.

Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at www.julabo.com.



## Quick start.

Individual JULABO consultation and comprehensive manuals at your disposal.



#### Quick support

If an error occurs, the integrated Black-Box function permits fast diagnosis by the JULABO service team



8

#### Space-saving footprint

All connections as well supply and exhaust air are located at the front or rear, no venting grids on the sides, units can be placed close to each other or the application

#### Satisfied customers.

11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.

#### 100% Checked.



100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.



#### For flammable bath fluid Classification III (FL) according to DIN 12876-1

#### 3





#### **Duplicate safety** Adjustable high temperature cut-off for internal

tank and for integrated expansion vessel



#### Continuous operation up to +40 °C Robust temperature control instrument, continuous operation even at ambient temperatures of up to +40 °C



#### Many interfaces.

Straight-forward remote control, data management, and integration into process structures. USB, Ethernet, RS232, SD card, and alarm off are permanently integrated. Further interfaces available as accessories.



#### Highest measuring accuracy

'Absolute Temperature Calibration' for manual compensation of a temperature difference, 3-point calibration



#### Full control

'Temperature Control Features', for individual optimization, access to all important control parameters, additional settings for band limit, limits, co-speedfactor etc.



#### 100 % Cooling capacity

'Active Cooling Control' for cooling available throughout the entire working temperature range, fast cool-down even at higher temperatures



#### Maximum safety.

Classification III according to DIN12876-1 enables safe operation, even with flammable fluids. Automatic switch-off in the event of high temperature or low liquid level.



#### Touch display. Perfect operation.

With the touch display, the user always has an overview of all values and functions. The intuitive and multilingual menu structure enables perfect control.



#### Intelligent pump system

Reliable and consistent pump capacity, electronically adjustable pump stages or pressure value, automatic adjustment of pump capacity to viscosity



#### **Control of the external application** External Pt100 sensor connection for precise measurement and control directly in the external application



#### Intelligent temperature control. Intelligent cascade control - automatic and selfoptimizing adaptation of the PID control parameters with external stability of +/- 0.05 °C.



#### Convenience for several users

Administrator level for customizing instrument settings, user levels with limited permissions for fast and safe defined access, password protection, all levels adjustable