# Julabo

# CORIO C-B17 Open heating bath circulator with stainless steel bath tank

The open heating bath circulators of the new CORIO series feature highquality bath tanks made of stainless steel.

#### **Product features**

- Bright, white, easy to read display
- Very quiet
- High-quality bath tanks made of stainless steel
- For internal applications
- Easy operation
- Integrated drain screw (except B5)
- Integrated drain screw



#### **Technical data**

Available voltage versions			Cooling	
Order No.	r No. 9 011 417		Cooling coil	accessory
Available voltage versions:				
9011417.22 100-115V/50-60Hz (Nema N5-15 Plug)				
9011417.33.chn	230V/50-60Hz (CN Plug)			
9011417.33	230V/50-60Hz (Schuko Plug - CEE 7/4 Plug Type F)			
9011417.04	230V/50-60Hz (UK Plug Type BS1363A)			
9011417.05	230V/50-60Hz ( 1011)	CH Plug Type SEV		
Bath			Other	
Bath tank		Stainless steel	Classification	Classification I (NFL)
Usable bath opening cm (W x L / D)		30 x 18 / 20	IP Code	IP 21
			Pump type	Immersion Pump
Electronics			Dimensions and volumes	
Temperature control		PID1	Weight kg	9.3
Absolute temperature calibration		1 Point Calibration	Dimensions cm (W × L × H)	38 x 40 x 47
Temperature display		LED	Filling volume l	13 17
Temperature setting		Keypad		
Temperature values				
Setting the resolution of the temperature display °C		0.1		
Working temperature range °C		+20 +100		
Temperature stability °C		±0.03		

# luiaha



<sup>1</sup> For applications near or below ambient temperature: use a cooling coil or JULABO immersion cooler.

### All Benefits



Brilliant.

Very bright display makes it easy to read even from a distance.



## Timer. Integrated.

CORIO circulators include an integrated timer function. When the set time has elapsed, a signal sounds and the device switches off. Setting range: 0 ... 999 minutes.



#### Exact.

You can rely on it. PID1 control and 'Active Cooling Control' make the new CORIO precise and perfect.



### Connection. Easy.

Inclined pump connections (M16×1) facilitate the connection of applications. Each unit includes 2 barbed fittings of 8/12 mm diameter each.



#### 100% Checked.

100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.



JULABO. Quality. Highest standards of quality for a long product life.



#### Satisfied customers.

11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



# Stable.

Rubber feet allow for a secured footing of your CORIO to prevent damage to your laboratory equipment.



Switch on. And off you go. Intelligent operating concept. Ready for operation with just a few quick and easy steps.



Everything at the front. All operating controls and safety functions are accessed easily and comfortably from the front.



Locked in. The lockable power plug guarantees safe connection. More process safety.



Early warning system for low liquid level Maximum safety for applications, optical and audible alarm, allows user to refill bath fluid before the unit shuts down



Green technology. Development consistently applied environmentally friendly materials and technologies.



#### Modern. Reliable.

High-grade components in every JULABO Circulator - platinum sensors, proven motor technology, CAN-Bus communication and much more.



Services 24/7.

Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at www.julabo.com.



#### Ouick start.

Individual JULABO consultation and comprehensive manuals at your disposal.