

CORIO CD-B33 Heating circulator with stainless steel open bath


The open heating bath circulators of the new CORIO series feature high-quality bath tanks made of stainless steel.



Product features


- Bright, white, easy to read display
- Very quiet
- easy switching between internal and external circulation
- USB connection
- High-quality bath tanks made of stainless steel
- For internal and external applications
- Integrated drain screw (except B5)
- Integrated pump connection M16×1
- Integrated drain screw

Heat-up time



Medium: Water

Pump capacity



Medium: Water

Technical data

Available voltage versions		Cooling	
Order No.	9 012 433	Cooling coil	accessory
Available voltage versions:			
9012433.01	100V/50-60Hz (Nema N5-15 Plug)		
9012433.02	115V/60Hz (Nema N5-15 Plug)		
9012433.03	230V/50Hz (Schuko Plug - CEE 7/4 Plug Type F)		
9012433.03.chn	230V/50Hz (CN Plug)		
9012433.04	230V/50Hz (UK Plug Type BS1363A)		
9012433.05	230V/50Hz (CH Plug Type SEV 1011)		
9012433.13	230V/60Hz (Nema N5-15 Plug)		
Bath		Other	
Bath tank	Stainless steel	Classification	Classification III (FL)
Bath cover	accessory	IP Code	IP 21

Usable bath opening cm (W x L / D) 66 x 32 / 15

Pump function Pressure Pump

Pump type Immersion Pump

Electronics	
Interfaces	USB
Temperature control	PID1
Absolute temperature calibration	1 Point Calibration
Temperature display	LED
Temperature setting	Keypad

Dimensions and volumes	
Weight kg	21
Barbed fittings inner diameter mm	8/12 mm
Dimensions cm (W x L x H)	91 x 36 x 43
Filling volume l	26 ... 39
Pump connections	M16x1 male

Temperature values	
Setting the resolution of the temperature display °C	0.1
Working temperature range °C	+20 ... +150
Temperature stability °C	±0.03
Ambient temperature °C ¹	+5 ... +40
Setting the resolution of the temperature display °C	0.01 ... 0.1

¹ For applications near or below ambient temperature: use a cooling coil or JULABO immersion cooler.

Included in delivery
 2 Barbed fittings for tubing 8 and 12 mm ID. (Pump connections M16x1 male)

All Benefits



Brilliant.
 Very bright display makes it easy to read even from a distance.



Switch on. And off you go.
 Intelligent operating concept. Ready for operation with just a few quick and easy steps.



Timer. Integrated.
 CORIO circulators include an integrated timer function. When the set time has elapsed, a signal sounds and the device switches off. Setting range: 0 ... 999 minutes.



Everything at the front.
 All operating controls and safety functions are accessed easily and comfortably from the front.



Exact.
 You can rely on it. PID1 control and 'Active Cooling Control' make the new CORIO precise and perfect.



Locked in.
 The lockable power plug guarantees safe connection. More process safety.



Connection. Easy.
 Inclined pump connections (M16x1) facilitate the connection of applications. Each unit includes 2 barbed fittings of 8/12 mm diameter each.



Early warning system for low liquid level
 Maximum safety for applications, optical and audible alarm, allows user to refill bath fluid before the unit shuts down



Connectivity.
 Remote control made easy. CORIO CD circulators feature a USB connection.



100% Checked.
 100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.



ATC.
Absolute Temperature Calibration, 1-point calibration (CD).




Green technology.
Development consistently applied environmentally friendly materials and technologies.



Internal. External.
The pump is controlled via a lever located directly below the display. Easily change between internal and external circulation.



JULABO. Quality.
Highest standards of quality for a long product life.



Modern. Reliable.
High-grade components in every JULABO Circulator – platinum sensors, proven motor technology, CAN-Bus communication and much more.



Satisfied customers.
11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



Services 24/7.
Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at www.julabo.com.



Stable.
Rubber feet allow for a secured footing of your CORIO to prevent damage to your laboratory equipment.



Quick start.
Individual JULABO consultation and comprehensive manuals at your disposal.