

CORIO CD-BC12 Heating circulator


for internal and external temperature applications with stainless steel bath tanks and working temperatures from +20 $^{\circ}\text{C}$ to +150 $^{\circ}\text{C}$

Product features


- Models for internal and external applications
- Bright, white, easy to read display
- Very quiet
- easy switching between internal and external circulation
- USB connection
- High-quality bath tanks made of stainless steel with bath lid and drain tap
- Integrated cooling coil for counter-cooling
- For internal and external applications
- Easy operation
- Integrated pump connection M16×1



Heat-up time



Pump capacity



Medium: Water

Technical data

Available voltage versions		Cooling	
Order No.	9 012 512	Cooling coil	integrated
Available voltage versions:			
9012512.01	100V/50-60Hz (Nema N5-15 Plug)		
9012512.02	115V/60Hz (Nema N5-15 Plug)		
9012512.03	230V/50Hz (Schuko Plug - CEE 7/4 Plug Type F)		
9012512.03.chn	230V/50Hz (CN Plug)		
9012512.04	230V/50Hz (UK Plug Type BS1363A)		
9012512.05	230V/50Hz (CH Plug Type SEV 1011)		
9012512.13	230V/60Hz (Nema N5-15 Plug)		
Bath		Other	



Bath tank	Stainless steel	Classification	Classification III (FL)
Bath cover	integrated	IP Code	IP 21
Usable bath opening cm (W x L / D)	22 x 15 / 20	Pump function	Pressure Pump
		Pump type	Immersion Pump

Electronics		Dimensions and volumes	
Interfaces	USB	Weight kg	12.2
Temperature control	PID1	Barbed fittings inner diameter mm	8/12 mm
Absolute temperature calibration	1 Point Calibration	Dimensions cm (W × L × H)	33 x 49 x 47
Temperature display	LED	Filling volume I	8.5 12
Temperature setting	Keypad	Pump connections	M16x1 male

Temperature values		
Setting the resolution of the temperature display °C	0.1	
Working temperature range °C	+20 +150	
Temperature stability °C	±0.03	
Ambient temperature $^{\circ}$ C 1	+5 +40	
Setting the resolution of the temperature display °C	0.01 0.1	
¹ For applications near or below ambient temperature: use a		

Included in delivery 2 Barbed fittings for tubing 8 and 12 mm ID. (Pump connections M16x1 male)

All Benefits



Brilliant

cooling coil or JULABO immersion cooler.

Very bright display makes it easy to read even from a distance.



Switch on. And off you go.

Intelligent operating concept. Ready for operation with just a few quick and easy steps.



Timer. Integrated.

CORIO circulators include an integrated timer function. When the set time has elapsed, a signal sounds and the device switches off. Setting range: 0 ... 999 minutes.



Everything at the front.

All operating controls and safety functions are accessed easily and comfortably from the front.



Exact.

You can rely on it. PID1 control and 'Active Cooling Control' make the new CORIO precise and perfect.



Locked in

The lockable power plug guarantees safe connection. More process safety.



Connection. Easy.

Inclined pump connections (M16×1) facilitate the connection of applications. Each unit includes 2 barbed fittings of $8/12\ mm$ diameter each.



Early warning system for low liquid level

Maximum safety for applications, optical and audible alarm, allows user to refill bath fluid before the unit shuts down





Connectivity.

Remote control made easy. CORIO CD circulators feature a USB connection.



100% Checked.

100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.



ATC.

Absolute Temperature Calibration, 1-point calibration (CD).



Handle with ease.

Makes day-to-day work easy. Comfortably move your JULABO Circulator around by using the ergonomic handles (front and rear).



Condensation protection.

Superb design solution. Integrated ventilation directs air over the bath lid and minimizes condensation.



Green technology.

Development consistently applied environmentally friendly materials and technologies.



Internal. External.

The pump is controlled via a lever located directly below the display. Easily change between internal and external circulation.



JULABO. Quality.

Highest standards of quality for a long product life.



Modern. Reliable.

High-grade components in every JULABO Circulator – platinum sensors, proven motor technology, CAN-Bus communication and much more.



Satisfied customers.

11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



Services 24/7.

Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at www.julabo.com.



Solid

Minimized energy loss through high-quality insulation.



Stable.

Rubber feet allow for a secured footing of your CORIO to prevent damage to your laboratory equipment.



Tidv.

The special drain tap for easy draining of bath fluids without tools.



Touching permitted.

Optimum safety. The ergonomic plastic handle protects your fingers from hot surfaces.



Quick start.

Individual JULABO consultation and comprehensive manuals at your disposal.