

# **CORIO CP-BC4 Heating circulator**


CORIO circulators offer professional technology for high demands. With these devices, temperature control is optionally possible in the internal bath or in a connected external application.

# **Product features**

- Models for internal and external applications
- Bright, white, easy to read display
- Very quiet
- easy switching between internal and external circulation
- · powerful and infinitely adjustable pressure pump
- USB connection
- RS232 interface for online communication
- High-quality bath tanks made of stainless steel with bath lid and drain tap
- Integrated pump connection M16×1
- Integrated cooling coil for counter-cooling
- Easy operation

# 450) (B)

# **Pump capacity**



Medium: Water

# Performance values

230V/50Hz (Schuko Plug - CEE 7/4 Plug Type F)		
Heating capacity kW	2	
Viscosity max. cSt	50	
Pump capacity flow rate I/min	8 27	
Pump capacity flow pressure bar	0.1 0.7	
Power consumption A	10	

# **Technical data**

Available voltage versions	Bath



Order No.	9 013 504	Bath tank	Stainless steel
Available voltage version	s:	Bath cover	integrated
9013504.33	200-230V/50-60Hz (Schuko Plug - CEE 7/4 Plug Type F)	Usable bath opening cm (W x L / D)	13 x 15 / 15
9013504.33.chn	200-230V/50-60Hz (CN Plug)		
9013504.04	200-230V/50-60Hz (UK Plug Type BS1363A)		
9013504.05	200-230V/50-60Hz (CH Plug Type SEV 1011)		
9013504.22	100-115V/50-60Hz (Nema N5-15 Plug)		

Other		Electronics	
Classification	Classification III (FL)	Interfaces	RS232, USB
Pump function	Pressure Pump	Temperature control	PID1
Pump type Immersion Pump	Absolute temperature calibration	3 Point Calibration	
		Temperature display	LED
		Temperature setting	Keypad
		Electronic Timer hr:min	0 999

Dimensions and volumes	
Weight kg	8.5
Barbed fittings inner diameter	8/12 mm
Dimensions cm (W $\times$ L $\times$ H)	23 x 41 x 42
Filling volume I	3 4.5
Pump connections	M16x1 male

Temperature values	
Setting the resolution of the temperature display °C	0.1
Working temperature range °C	+20 +200
Temperature stability °C	±0.02
Ambient temperature °C	+5 +40
Temperature display resolution °C	0.01 0.1

# Included in delivery

2 Barbed fittings for tubing 8 and 12 mm ID. (Pump connections M16x1 male)

For applications near or below ambient temperature: use a cooling coil or JULABO immersion cooler.

# **All Benefits**



#### Rrilliant

Very bright display makes it easy to read even from a distance.



## Switch on. And off you go.

Intelligent operating concept. Ready for operation with just a few quick and easy steps.



# Timer. Integrated.

CORIO circulators include an integrated timer function. When the set time has elapsed, a signal sounds and the device switches off. Setting range: 0 ... 999 minutes.



## Everything at the front.

All operating controls and safety functions are accessed easily and comfortably from the front.



#### Exact.

You can rely on it. PID1 control and 'Active Cooling Control' make the new CORIO precise and perfect.



### Locked in.

The lockable power plug guarantees safe connection. More process safety.





#### Connection. Easy.

Inclined pump connections (M16×1) facilitate the connection of applications. Each unit includes 2 barbed fittings of 8/12 mm diameter each.



#### Powerful. Adjustable.

Strong pressure pump, continuously adjustable.



### Early warning system for low liquid level.

Maximum safety for your application. Optical and audible alarm allows user to refill bath fluid in time.



#### Connectivity.

Remote control made easy. CORIO CP circulators feature a USB connection and RS232 interface.



#### Condensation protection.

Superb design solution. Integrated ventilation directs air over the bath lid and minimizes condensation.



#### Handle with ease.

Makes day-to-day work easy. Comfortably move your JULABO Circulator around by using the ergonomic handles (front and rear).



#### Internal, External,

The pump is controlled via a lever located directly below the display. Easily change between internal and external circulation.



#### Solid.

Minimized energy loss through high-quality insulation.



#### Stable.

Rubber feet allow for a secured footing of your CORIO to prevent damage to your laboratory equipment.



#### Tidy.

The special drain tap for easy draining of bath fluids without tools.



## Touching permitted.

Optimum safety. The ergonomic plastic handle protects your fingers from hot surfaces.



#### 100% Checked.

100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.



## Green technology.

Development consistently applied environmentally friendly materials and technologies.



# JULABO. Quality.

Highest standards of quality for a long product life.



# Quick start.

Individual JULABO consultation and comprehensive manuals at your disposal.



# Satisfied customers.

11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



#### Services 24/7

Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at www.julabo.com.



# Highest measuring accuracy

'Absolute Temperature Calibration' for manual compensation of a temperature difference, 3-point calibration