

FL2506 Powerful model in tower version

The FL models shown here have higher cooling capacity, powerful circulating pumps, and internal bath volumes of up to 30 liters. 2 variants: Air-cooled (FL) and water-cooled (FLW).

Optional heating function


On request, we also offer our FL recirculating chillers with an additional integrated heating function and other special solutions. Our product experts will be happy to advise you individually in order to design a temperature control unit that is exactly right for your needs. Just give us a call!



Product features

- Ergonomic design and easy operation
- Splash-proof keypad
- · Large, bright LED display
- Reliable Microprocessor PID temperature control
- Precise PID temperature control
- Powerful immersion pumps, suitable for continuous operation
- Permissible temperature in return line +80°C
- · Easy filling from the top with hinged protective lid
- Low liquid level protection with optical and audible alarm signal
- Integrated stainless steel bath tanks
- Front drain
- No side vents, instruments can be placed right next to other equipment
- RS232 interface for PC connection
- IP class according to IEC 60529: 21
- Alarm output, potential-free change-over contact (max. 30 VA)
- Pressure Indicator

Pump capacity



Medium: Water





Performance values

| 230V/50Hz (Schuko Plug - CEE 7/4 Plug Type F) | | | |
|---|-------|--|--|
| Pump capacity flow rate I/min | 60 | | |
| Pump capacity flow pressure bar | 0.5 6 | | |
| Power consumption A | 14 | | |

| Order No. | | 9666025.03 | 9666025.03 | | |
|------------------------------------|--------|------------|------------|-----|--|
| Cooling capacity (Ethanol) | | | | | |
| °C | 20 | 10 | 0 | -10 | |
| kW ¹ | 2.5 | 1.9 | 1 | 0.3 | |
| Refrigerant stage 1 | | | | | |
| Refrigerant | R452A | | | | |
| Filling weight g | 1510 | | | | |
| Global Warming Potential for R452A | 2140 | | | | |
| Carbon dioxide equivalent t | 3.2314 | | | | |

¹ Performance specifications measured in accordance with DIN 12876. Cooling capacities up to 20 °C measured with ethanol; over 20 °C with thermal oil unless otherwise specified. Performance specifications apply at an ambient temperature of 20 °C. Performance values may differ with other bath fluids.

Technical data

| Available voltage versions | | Cooling | | |
|-------------------------------------|------------------------------------|--------------------------------|---|------------------------|
| Order No. | 9 666 025 | | Cooling of compressor | 1-stage Air |
| Available voltage versions: | | | | |
| 9666025.13 | 230V/60Hz (Nema | a N6-20 Plug) (R449A) | | |
| 9666025.03 | 230V/50Hz (Schu Type F) (R452A) | ko Plug - CEE 7/4 Plug | | |
| Bath | | | Other | |
| Bath tank | | Stainless steel | Sound pressure level dbA | 64 |
| | | | Classification | Classification I (NFL) |
| | | | IP Code | IP 21 |
| | | | Pump type | Immersion Pump |
| | | | | |
| Electronics | | | Dimensions and volumes | |
| | | Alarm output, RS232, Stakei | Weight kg | 158 |
| | | | Barbed fittings inner diameter mm | 1" |
| Temperature control | | PID1 | Dimensions cm (W \times L \times H) | 60 x 76 x 115 |
| Temperature display | | LED | Filling volume I | 24 30 |
| Temperature setting | | Keypad | Pump connections | G1¼" male |
| | | | | |
| Temperature value | es . | | Included in delivery | |
| Setting the resolution o display °C | f the temperature | 0.1 | 2 each barbed fittings for tubing 1" inner dia (pump connections G1 $1/4\mbox{"}$ male). | |
| Return flow temperature | e max. °C | 80 | | |
| | | | | |



| Temperature stability °C | ±0.5 |
|--|--------|
| Ambient temperature °C | +5 +40 |
| Setting the resolution of the temperature display °C | 0.1 |

All Benefits



100% Checked.

100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.



Green technology.

Development consistently applied environmentally friendly materials and technologies.



JULABO. Quality.

Highest standards of quality for a long product life.



Quick start.

Individual JULABO consultation and comprehensive manuals at your disposal.



Satisfied customers.

11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



Services 24/7.

Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at www.julabo.com.



Precise

PID Temperature control with set control parameters, temperature stability $\pm 0.02... \pm 0.2$ °C



Connection of additional equipment

Stakei connections for solenoid valve