

FC1200T Chiller

FC recirculating coolers with a particularly powerful pump and Pt100 connection are preferably used for precise temperature control of large-volume external applications. They can be integrated into process control systems via the permanently integrated analog connection.

Product features

- Adjustable ratio for feed/return temperatures
- · Easy filling system located at the front
- · Activation of pump for filling
- Bright MULTI-DISPLAY (LED)
- Upper and lower temperature warning functions with interval tone
- Integrated freezing protection and dry-running protection
- Rapid and easy operation via seamless, splash-proof keypad
- Liquid level indication on the front
- Self-test, reciprocal sensor monitoring, pump motor and compressor overload protection
- Complete shut-down with audible signal in case of an alarm
- removable venting grid for simplified removal of dust
- RS232 interface for PC connection
- High temperature stability
- Integrated heater with 1.2 kW capacity
- · Connections for external Pt100 sensor
- Analog Connections for programming (0..10V / 0...24mA) and temperature recorder (0V = 0°C)
- Pressure Indicator

Performance values

230V/50Hz (Schuko Plug - CEE 7/4 Plug Type F)				
Heating capacity kW	1.2			
Pump capacity flow rate I/min	28			
Pump capacity flow pressure bar	3.5			
Power consumption A	8			





Order No.			9600126.03				
Cooling capacity (Ethanol)							
°C	20	10	5	0	-10		
kW ¹	1.1	0.75	0.55	0.45	0.15		
Refrigerant stage 1							
Refrigerant	R134a						
Filling weight g	720						
Global Warming Potent R134a	tial for 1430						
Carbon dioxide equival	ent t 1.0296						

¹ Performance specifications measured in accordance with DIN 12876. Cooling capacities up to 20 °C measured with ethanol; over 20 °C with thermal oil unless otherwise specified. Performance specifications apply at an ambient temperature of 20 °C. Performance values may differ with other bath fluids.

Technical data							
Available voltage versions			Cooling				
Order No.	9 600 126		Cooling of compressor	1-stage Air			
Available voltage versions:							
9600126.03	230V/50Hz (Schuko Plug - CEE 7/4 Plug Type F) (R134a)						
9600126.04	230V/50Hz (UK Plug Type BS1363A) (R134a)						
9600126.05	230V/50Hz (CH Pl (R134a)	ug Type SEV 1011)					
Bath			Other				
Bath tank		Stainless steel	Sound pressure level dbA	58			
			Classification	Classification III (FL)			
			IP Code	IP 21			
			Pump type	Immersion Pump			
Florence			Dimensional and columns				
Electronics		Dimensions and volumes					
Interfaces		Alarm output, Profibus optional, REG/EPROG,	Weight kg	67			
		RS232, Stakei, Standby-Input	Barbed fittings inner diameter mm	8/12 mm			
External nt100 concer	connection	integrated	Dimensions cm (W × L × H)	46 x 61 x 49			
·		PID1	Filling volume I	8 11			
		2x LED	Pump connections	M16x1 male			
		Keypad					
remperature setting		Кеурий					
Temperature values		Included in delivery					
Working temperature range °C $-10 \dots +80$ Temperature stability °C ± 0.2		2 Barbed fittings for tubing 8 and 12 mm ID. (Pump connections					
		±0.2	M16x1 male)				
Ambient temperature	°C	+5 +40					
Setting the resolution display °C	of the temperature	0.1					



All Benefits



100% Checked.

100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.



Green technology.

Development consistently applied environmentally friendly materials and technologies.



100 % Cooling capacity

'Active Cooling Control' for cooling available throughout the entire working temperature range, fast cool-down even at higher temperatures



Control of the external application

External Pt100 sensor connection for precise measurement and control directly in the external application



For flammable bath fluid

Classification III (FL) according to DIN 12876-1



JULABO. Quality.

Highest standards of quality for a long product life.



Quick start.

Individual JULABO consultation and comprehensive manuals at your disposal.



Satisfied customers.

11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



Services 24/7.

Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at www.julabo.com.



For higher demands

PID Temperature control with drift compensation and adjustable parameters, improved temperature stability for external applications, temperature stability ± 0.01 °C internal, $<\pm 0.1$ °C external.



Early warning system for high/low temperature limits

Maximum safety for applications, optical and audible alarm, convertible to automated cut-off function



Connection of additional equipment Stakei connections for solenoid valve