

## PRESTO A80t Process system

As air- or water-cooled versions, the units with 2-stage refrigeration unit offer high cooling and heating capacities for lowest temperatures down to -80 °C.


The highly dynamic temperature control systems PRESTO are designed for high-precision temperature control for a wide range of applications such as reactor vessels or material stress tests. Moreover, by using efficient components, the process systems can compensate exothermic and endothermic reactions exceptionally fast. Permanent internal monitoring and self-lubricating pumps ensure a long life-time. In addition, numerous interfaces offer many remote control possibilities across networks or for integration into higher-level control systems.



### Product features


- Analog connections, RS485, Profibus DP (accessory)
- Space optimized design creates more room directly next to the units
- External Pt100 sensor connection
- Built-in 5.7" industrial color touchscreen
- Second external Pt100 sensor connection (accessory)
- Alarm output
- Temperature stability  $\pm 0.01$  °C ...  $\pm 0.05$  °C
- Pump pressure up to 1.7 bar, max. flow rate 40 l/min
- Heating capacity up to 3.4 kW
- Cooling capacity up to 1.2 kW
- removable ventilation grid

### Cool-down time




Medium: Thermal HL

### Heat-up time



Medium: Thermal HL

### Pump capacity



## Performance values

400V/3PNPE/50Hz (Plug 16A CEE)	
Heating capacity kW	3.4
Viscosity max. cSt	50
Pump capacity flow rate l/min	0 ... 40
Pump capacity flow pressure bar	0.1 ... 1.7
Power consumption A	16

## Refrigerant variants

Order No.		9420801.07.T						
Cooling capacity (Ethanol)								
°C	200	20	0	-20	-30	-40	-60	-80
kW <sup>1</sup>	1.2	1.2	1.2	1.1	1.1	1.1	0.65	0.1
Refrigerant stage 1				Refrigerant stage 2				
Refrigerant	R507			Refrigerant	R23			
Filling weight g	1140			Filling weight g	500			
Global Warming Potential for R507	3985			Global Warming Potential for R23	14800			
Carbon dioxide equivalent t	4.5429			Carbon dioxide equivalent t	7.4			

Order No.		9420801.S1.07.T					
Cooling capacity (Ethanol)							
°C	20	0	-20	-30	-40	-60	
kW <sup>1</sup>	1.3	1.2	1.1	1.1	1	0.7	
Refrigerant stage 1				Refrigerant stage 2			
Refrigerant	R449A			Refrigerant	R23		
Filling weight g	1140			Filling weight g	500		
Global Warming Potential for R449A	1397			Global Warming Potential for R23	14800		
Carbon dioxide equivalent t	1.59258			Carbon dioxide equivalent t	7.4		

<sup>1</sup> Performance specifications measured in accordance with DIN 12876. Cooling capacities up to 20 °C measured with ethanol; over 20 °C with thermal oil unless otherwise specified. Performance specifications apply at an ambient temperature of 20 °C. Performance values may differ with other bath fluids.

## Technical data

Available voltage versions		Cooling	
Order No.	9 420 801.T	Cooling of compressor	2-stage Air
Available voltage versions:			
9420801.07.T	400V/3PNPE/50Hz (Plug 16A CEE) (R507)		
9420801.S1.07.T	400V/3PNPE/50Hz (Plug 16A CEE) (R449A)		
9420801.16.T	208-220V/3PPE/60Hz (Without Plug) (R507)		
9420801.06.T	230V/3PPE/50Hz (Plug 32A CEE) (R507)		

Other	
Sound pressure level dbA	68
Classification	Classification III (FL)
IP Code	IP 20
Pump type	Centrifugal Pump
Pump type Magnetically coupled	1

Electronics	
Interfaces	Alarm output, Ethernet, Modbus, Profibus optional, REG/EPROG optional, RS232, RS485 optional, SD memory card, Standby-Input optional, USB
External pt100 sensor connection	integrated
2nd external Pt100 sensor connection	accessory
Integrated programmer	8x60 steps
Temperature control	ICC
Absolute temperature calibration	3 Point Calibration
Temperature display	5.7" TFT Touchscreen
Temperature setting	Touchscreen

Dimensions and volumes	
Internal usable expansion volume l	5.6
Minimal process volume l	3.9
Active heat exchanger volume l	1.7
Weight kg	167
Dimensions cm (W x L x H)	43 x 65 x 126
Pump connections	M24x1.5 male

Temperature values	
Setting the resolution of the temperature display °C	0.01
Working temperature range °C	-80 ... +250
Temperature stability °C	±0.01 ... ±0.05
Ambient temperature °C	+5 ... +40
Setting the resolution of the temperature display °C	0.01

### All Benefits



**Touch display. Perfect operation.**  
With the touch display, the user always has an overview of all values and functions. The intuitive and multilingual menu structure enables perfect control.



**Convenience for several users**  
Administrator level for customizing instrument settings, user levels with limited permissions for fast and safe defined access, password protection, all levels adjustable



**100 % Cooling capacity**  
'Active Cooling Control' for cooling available throughout the entire working temperature range, fast cool-down even at higher temperatures



**Intelligent temperature control.**  
Intelligent cascade control - automatic and self-optimizing adaptation of the PID control parameters with external stability of +/- 0.05 °C.



**Full control**  
'Temperature Control Features', for individual optimization, access to all important control parameters, additional settings for band limit, limits, co-speedfactor etc.



**Control of the external application**  
External Pt100 sensor connection for precise measurement and control directly in the external application



**Highest measuring accuracy**  
'Absolute Temperature Calibration' for manual compensation of a temperature difference, 3-point calibration



**Intelligent pump system**  
Reliable and consistent pump capacity, electronically adjustable pump stages or pressure value, automatic adjustment of pump capacity to viscosity



**Many interfaces.**  
Straight-forward remote control, data management, and integration into process structures. USB, Ethernet, RS232, SD card, and alarm off are permanently integrated. Further interfaces available as accessories.



**Space-saving footprint**  
All connections as well supply and exhaust air are located at the front or rear, no venting grids on the sides, units can be placed close to each other or the application



**Continuous operation up to +40 °C**  
Robust temperature control instrument, continuous operation even at ambient temperatures of up to +40 °C



**Maximum safety.**  
Classification III according to DIN12876-1 enables safe operation, even with flammable fluids. Automatic switch-off in the event of high temperature or low liquid level.



**Duplicate safety**  
Adjustable high temperature cut-off for internal tank and for integrated expansion vessel



**For flammable bath fluid**  
Classification III (FL) according to DIN 12876-1



**Quick support**  
If an error occurs, the integrated Black-Box function permits fast diagnosis by the JULABO service team



**100% Checked.**  
100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.



**Green technology.**  
Development consistently applied environmentally friendly materials and technologies.



**JULABO. Quality.**  
Highest standards of quality for a long product life.



**Quick start.**  
Individual JULABO consultation and comprehensive manuals at your disposal.



**Satisfied customers.**  
11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



**Services 24/7.**  
Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at [www.julabo.com](http://www.julabo.com).