

PRESTO W92ttx Process system

The W92 class process systems are extremely powerful and can also simulate extreme environmental conditions. They are used, for example, in the temperature control of vacuum chambers for component testing in the aerospace industry.


The highly dynamic temperature control systems PRESTO are designed for high-precision temperature control for a wide range of applications such as reactor vessels or material stress tests. Moreover, by using efficient components, the process systems can compensate exothermic and endothermic reactions exceptionally fast. Permanent internal monitoring and self-lubricating pumps ensure a long life-time. In addition, numerous interfaces offer many remote control possibilities across networks or for integration into higher-level control systems.



Product features

- Cooling capacity up to 31 kW
- Ambient temperature range +5 °C to +40 °C
- Optional analog connections, RS485, Profibus DP, Modbus
- External Pt100 sensor connection
- Analog connections, RS485, Profibus DP (accessory)
- Built-in 5.7" industrial color touchscreen
- Alarm output
- Second external Pt100 sensor connection (accessory)
- Intelligent warning and safety functions
- Pump pressure up to 5.5 bar, max. flow rate 70 l/min

Pump capacity





Performance values

400V/3PNPE/50Hz (Without Plug)	
Heating capacity kW	36
Viscosity max. cSt	70
Pump capacity flow rate I/min	0 70
Pump capacity flow pressure bar	0.1 5.5
Power consumption A	66

efrigerant varia	ants						
Order No.				9421923.07.TT			
Cooling capacity	(Ethanol)						
°C	200	20	0	-20	-40	-60	-80
kW ¹	31	27	20	11	10.5	8	2
Refrigerant stage 1			Refrigerant stag	e 2			
Refrigerant		R404A		Refrigerant		R23	
Filling weight g		4500		Filling weight g		1250	
Global Warming F R404A	Potential for	3922		Global Warming R23	Potential for	14800	
Carbon dioxide equivalent t		17.649		Carbon dioxide equivalent t		18.5	
Order No.	r No. 9421923.S1.07.TT						
Cooling capacity	(Ethanol)						
°C	20	0	-20	-40	-60	-80	-90
kW ¹	26	17	11	10.5	8	2	0.8
Refrigerant stage	1			Refrigerant stag	e 2		
Refrigerant		R449A		Refrigerant		R23	
Filling weight g		4500		Filling weight g		1250	
Global Warming F R449A	Potential for	1397		Global Warming Potentia R23		14800	

¹ Performance specifications measured in accordance with DIN 12876. Cooling capacities up to 20 °C measured with ethanol; over 20 °C with thermal oil unless otherwise specified. Performance specifications apply at an ambient temperature of 20 °C. Performance values may differ with other bath fluids.

Technical data

Available voltage versions		Cooling		
Order No.	9 421 923.TT	Cooling of compressor	2-stage Water	
Available voltage versions:		Cooling water pressure max. bar	6	
9421923.07.TT	400V/3PNPE/50Hz (Without Plug) (R404A)	Max. heat dissipated by unit into cooling water kW	50	
9421923.S1.07.TT	400V/3PNPE/50Hz (Without Plug) (R449A)	Recommended cooling water properties		
9421923.17.TT	480V/3P(N)PE/60Hz (Without Plug) (R404A)	Cooling water temperature range °C	10 15	
		Cooling water difference pressure bar	1.5 6	
		Cooling water consumption I/min ²	43	
		Permissible cooling water properties		



Cooling water temperature range °C	5 35
Cooling water difference pressure bar ³	0.5 6

 $^{^{\}rm 2}$ Cooling water consumption may vary outside recommended cooling water properties.

 $^{^{\}rm 3}$ At cooling water temperatures of 25 °C and higher, the minimum differential pressure is 1 bar.

Other		Electronics		
Sound pressure level dbA	74	Interfaces	Alarm output,	
Classification	Classification III (FL)		Ethernet, Modbus, RS232, SD memory	
IP Code	IP 21		card, USB	
Pump type	Gear Pump	External pt100 sensor connection	integrated	
Pump type Magnetically coupled	1	2nd external Pt100 sensor connection	accessory	
		Integrated programmer	8x60 steps	
		Temperature control	ICC	
		Absolute temperature calibration	3 Point Calibration	
		Temperature display	5.7" TFT Touchscreen	
		Temperature setting	Touchscreen	
Dimensions and volumes		Temperature values		
Internal usable expansion volume I	40	Setting the resolution of the temperature	0.01	
Minimal process volume I	28	display °C		
Active heat exchanger volume I	16	Working temperature range °C	-92 + 250	
Weight kg	870	Temperature stability °C	±0.05 ±0.2	
Cooling Water Connection in	G3⁄4	Ambient temperature °C	+5 +40	
Dimensions cm (W x I x H)	05 v 127 v 100	Setting the resolution of the temperature	0.01	

All Benefits

Dimensions cm (W × L × H)

Pump connections



Touch display. Perfect operation.

With the touch display, the user always has an overview of all values and functions. The intuitive and multilingual menu structure enables perfect control.

95 x 127 x 190

M38x1.5 male



display °C

Convenience for several users

Administrator level for customizing instrument settings, user levels with limited permissions for fast and safe defined access, password protection, all levels adjustable



100 % Cooling capacity

'Active Cooling Control' for cooling available throughout the entire working temperature range, fast cool-down even at higher temperatures



Intelligent temperature control.

Intelligent cascade control - automatic and selfoptimizing adaptation of the PID control parameters with external stability of +/- 0.05 °C.



Full control

'Temperature Control Features', for individual optimization, access to all important control parameters, additional settings for band limit, limits, co-speedfactor etc.



Control of the external application

External Pt100 sensor connection for precise measurement and control directly in the external application





Highest measuring accuracy

'Absolute Temperature Calibration' for manual compensation of a temperature difference, 3-point calibration



Intelligent pump system

Reliable and consistent pump capacity, electronically adjustable pump stages or pressure value, automatic adjustment of pump capacity to viscosity



Many interfaces.

Straight-forward remote control, data management, and integration into process structures. USB, Ethernet, RS232, SD card, and alarm off are permanently integrated. Further interfaces available as accessories.



100% Checked.

100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.



Green technology.

Development consistently applied environmentally friendly materials and technologies.



JULABO. Quality.

Highest standards of quality for a long product life.



Quick start.

Individual JULABO consultation and comprehensive manuals at your disposal.



Space-saving footprint

All connections as well supply and exhaust air are located at the front or rear, no venting grids on the sides, units can be placed close to each other or the application



Satisfied customers.

11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



Services 24/7.

Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at www.julabo.com.



Continuous operation up to +40 °C

Robust temperature control instrument, continuous operation even at ambient temperatures of up to +40 °C



Maximum safety.

Classification III according to DIN12876-1 enables safe operation, even with flammable fluids.

Automatic switch-off in the event of high temperature or low liquid level.



Duplicate safety

Adjustable high temperature cut-off for internal tank and for integrated expansion vessel



For flammable bath fluid

Classification III (FL) according to DIN 12876-1



Quick support

If an error occurs, the integrated Black-Box function permits fast diagnosis by the JULABO service team