

Model WIC 2 | Walk-in-chambers for stability testing according to ICH (Q1A)

The walk-in-chambers offer a wide range of features and benefits to perfectly meet requirements in stability testing. Perfect test conditions are maintained in a wide range of temperature from 10°C to 50°C and relative humidity of 20% to 90% RH.

BENEFITS

- · Stable and uniform environment
- Fully complies with Pharma regulations (ICH)Equipment
- Longevity corrosion resistant
- · Ease of operation
- Environmental friendly refrigerant with GWP value 547
- · Maintenance possible with the least possible disruption to the climate conditioning
- Perfectly meets requirements in Pharma industry
- · 3 years warranty



Model 2



Model 2

IMPORTANT FEATURES

- Relative humidity accuracy of ± 2.5%
- Temperature accuracy of ± 1.5°C
- Duct work for proper distribution of air
- Highly insulated room panels with U value of only 0,21 W/m^2K
- LED Lighting with motion detector
- · High quality room elements, made in Germany
- Interior completely stainless steel

- · Exterior service accessibility
- Room Elements: Galvanized sheet steel, polyester coated, white, similar to RAL 9010, interior surfaces in stainless steel,
- 4 inch / 100 mm PU foam U value: 0,21W/m 2 K
- Floor: Floor overlay is chrome-nickel steel, pattern-rolled 5WL
- Surface load: 50.000 N/m²

ORDERING INFORMATION

| Interior volume [L] | Power supply - unit fuse | Plug* | Version | Model version | ArtNo. |
|------------------------|---------------------------|--------------|-----------------------------|---------------|-----------|
| Model WIC 2 | | | | | |
| 18,523 | 230 V 1~ 50 Hz -20,0 A | fixed supply | Standard | WIC2-230V | 9800-0012 |
| | 208230 V 1~ 60 Hz -20,0 A | fixed supply | Standard | WIC2-208V | 9800-0003 |
| | | | with conditioner on ceiling | WIC2C-208V | 9800-0004 |




TECHNICAL DATA

| TECHNICAL DATA | | | | | |
|---|------------------------------|--------------|-----------------------------|--|--|
| Data | | | | | |
| Designation | WIC2-230V | WIC2-208V | WIC2C-208V | | |
| Article Number | 9800-0012 | 9800-0003 | 9800-0004 | | |
| Option model | Standard | Standard | with conditioner on ceiling | | |
| Performance Data Temperature | Performance Data Temperature | | | | |
| Temperature range | {3299}{3298} | {3299}{3298} | {3299}{3298} | | |
| Performance Data Climate | | | | | |
| Temperature range with humidity | 1050 °C | 1050 °C | 1050 °C | | |
| Humidity range | 2090 % RH | 2090 % RH | 2090 % RH | | |
| Temperature uniformity at 25°C and 60% RH | 1.5 ± K | 1.5 ± K | 1.5 ± K | | |
| Temperature uniformity at 40°C and 75% RH | 1.5 ± K | 1.5 ± K | 1.5 ± K | | |
| Temperature fluctuation at 25°C and 60% RH | 0.5 ± K | 0.5 ± K | 0.5 ± K | | |
| Temperature fluctuation at 40°C and 75% RH | 0.5 ± K | 0.5 ± K | 0.5 ± K | | |
| Electrical data | | | | | |
| Rated Voltage | 230 V | 208230 V | 208230 V | | |
| Power frequency | 50 Hz | 60 Hz | 60 Hz | | |
| Nominal power | 2,7 kW | 2,7 kW | 2,7 kW | | |
| Unit fuse | 20,0 A | 20,0 A | 20,0 A | | |
| Phase (Nominal voltage) | 1~ | 1~ | 1~ | | |
| Dimensions and weights | | | | | |
| Interior volume | 18,523 L | 18,523 L | 18,523 L | | |
| Net weight of the unit (empty) | 981 kg | 981 kg | 981 kg | | |
| Housing dimensions not incl. fittings and con | nections | | | | |
| Width net | 2,600 mm | 2,600 mm | 2,600 mm | | |
| Height net | 2,470 mm | 2,470 mm | 2,470 mm | | |
| Depth net | 3,600 mm | 3,600 mm | 3,600 mm | | |
| Internal Dimensions | | | | | |
| Interior width | 2,400 mm | 2,400 mm | 2,400 mm | | |
| Interior height | 2,270 mm | 2,270 mm | 2,270 mm | | |
| | | | | | |




| Interior depth | 3,400 mm | 3,400 mm | 3,400 mm |
|---------------------------------------|------------|------------|------------|
| Unit doors | 1 | 1 | 1 |
| Environment-specific data | | | |
| Energy consumption at 40°C and 75% RH | 1,140 Wh/h | 1,140 Wh/h | 1,140 Wh/h |

DIMENSIONS Incl. fittings and connections [mm]



DIAGRAMS



Climate chart



ACCESSORIES

| Designation | Description | WIC 2 | * | ArtNo. |
|-------------------------|---|-------|---|-----------|
| Measuring station | with 1x PT100 for humidity | • | - | 8012-2579 |
| Options/Accessories | | • | - | 8012-2461 |
| Qualification documents | IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature and humidity values | | | |
| | Digital in PDF format | • | - | 7057-0002 |
| | Hard copy inside folder | • | - | 7007-0002 |
| Ramp for all WIC models | | • | - | 8012-2155 |
| | suitable for all WIC models | • | - | 8012-2239 |
| Shelf set middle | suitable for WIC 2, WIC 2 C | • | - | 8012-2157 |
| | | • | - | 8012-2241 |

SERVICES

| Designation | Description | * | ArtNo. |
|---|---|---|-----------|
| | 1 access port with silicone plug, 30 mm - position of your choice | - | DL10-1000 |
| | 1 access port with silicone plug, 50 mm - your choice of position | - | DL10-1050 |
| | 2 access ports with silicone plugs, 30 mm - your choice of position | - | DL10-1010 |
| | 2 access ports with silicone plugs, 50 mm - your choice of position | - | DL10-1060 |
| | 3 access ports with silicone plugs, 30 mm - your choice of position | - | DL10-1020 |
| Access port with silicone plug | 3 access ports with silicone plugs, 50 mm - your choice of position | - | DL10-1070 |
| | 4 access ports with silicone plugs, 30 mm - your choice of position | - | DL10-1030 |
| | 4 access ports with silicone plugs, 50 mm - your choice of position | - | DL10-1080 |
| | 5 access ports with silicone plugs, 30 mm - your choice of position | - | DL10-1040 |
| | 5 access ports with silicone plugs, 50 mm - your choice of position | - | DL10-1090 |
| Calibration services | | | |
| Temperature and humidity measurement, 13-1 measuring points | Temperature measurement with 13 temperature measuring points and 1 humidity measuring point in center of chamber with a pair of values specified by the user, including certificate | - | DL30-0113 |
| Installation services | | | |
| Installation and Comissioning | Installation and Comissioning | - | DL10-0800 |
| Maintenance services | | | |



| Designation | Description | * | ArtNo. |
|---------------------|---|---|-----------|
| Maintenance | One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate | - | DL20-1000 |
| Validation services | | | |
| Execution of IQ/OQ | Execution of IQ/OQ in accordance with qualification folder | - | DL40-0200 |



BINDER GmbH

Tuttlingen, Germany TEL +49 7462 2005 o info@binder-world.com www.binder-world.com BINDER Inc.

Bohemia, NY, USA TEL +1 631 224 4340 usa@binder-world.com www.binder-world.us BINDER Environmental Testing Equipment (Shanghai) Co., Ltd.

Shanghai, P.R. China TEL +86 21 685 808 25 china@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China TEL +852 39070500 asia@binder-world.com www.binder-world.com